

# HYDR8




## 4i Touchless Sensor-Activated Water Purification System

### HYDR8 4i Specifications



- ▶ Weight  
69.9 lbs (31.7 kgs)
- ▶ Dimensions  
50.9" H x 14" W x 17" L  
(1293mm H x 355.6mm W x 431.8mm L)
- ▶ Cold Tank Capacity  
3 gallons  
(11 Liters)
- ▶ Hot Tank Capacity  
0.5 gallons  
(2 Liters)
- ▶ Dispense Area  
12" tall (305mm)
- ▶ Recommended Water Pressure  
60-70 PSI
- ▶ Rated Voltage/Frequency  
120v/60hz |  
220v/50hz
- ▶ Power Consumption  
120v/60hz |  
220v/50hz

### → The HYDR8 Water Purification Process



\*Optional Recommendations

Invigor8 BOOST™: Electrolyte & Alkalinity Enhancement (Adds Potassium, Calcium, Magnesium & Sodium).

Reverse Osmosis Membrane: Removes PFAS, Lead, Legionella, Arsenic, Fluoride & many other toxic contaminants.



Our systems are tested and certified to the highest industry standards for safety and performance. The 4i is certified by IAPMO in accordance with ANSI/NSF 372 for lead free products and certified by IAPMO R&T in accordance with UL 399 and CSA 22.2 for electrical safety.

329 38th St 2nd Fl Brooklyn NY 11232

[www.hydr8.us](http://www.hydr8.us)

718-313-0113

# 4i : Touchless Water Purification System



## Touchless Sensor Activation

Hygienic, touch-free operation.



## Anti-Microbial Surface

Anti-microbial additive maintains cleanliness of unit exterior.



## High-Capacity Drip Tray

Optional drain connection prevents need for emptying.



< **4i-CT**  
Countertop  
Option Now  
Available!



11.7"W x 19.5"D x 17.8"H



## Advanced Purification Technology

Proprietary, multi-stage, reverse osmosis process is certified to industry standards.



## Activated Oxygen Self-Cleaning

Advanced technology circulates water and cleans tanks and lines to maintain water freshness.




## 24/7 System Monitoring

Continuous monitoring of system performance and water quality with real-time status displayed on LCD screen and bluetooth compatible service app.



# Decontamin8

→ Advanced Hygiene Feature  
*optional*



When "Decontamin8" is activated the HYDR8 4i system will initiate a deep-self-cleaning mode during periods of extended non-usage.

This makes the HYDR8 4i a perfect fit for businesses with satellite offices with hybrid office hours, schools & organizations that regularly break for the holidays.

### HOW IT WORKS :

A concentrated amount of activated oxygen is injected into the cold water reservoir. That water is then automatically dispensed into the drain-connected drip tray cleaning the entire system.



Get Your Quote Today!

# HYDR8



Call Us Now:

**718-313-0113**