


THE HYDR8 WATER PURIFICATION PROCESS



SEDIMENT FILTER

REDUCES PARTICLES SUCH AS DIRT, SILT, PIPE RUST PRE-CARBON FILTER REDUCES CHLORINE, CHEMICALS AND PESTICIDES

REVERSE OSMOSIS (RO) MEMBRANE

CAPTURES CONTAMINANTS SUCH AS DISSOLVED SOLIDS,

ARSENIC, LEAD, PHARMACEUTICALS, AND METALS

GA CARBON FINAL POLISH FILTER

COCONUT SHELL CARBON POLISHES WATER FOR GREAT TASTE

INVIGOR8 BOOSTTM MINERAL ALKALINE FILTER

RESTORES ELECTROLYTES SUCH AS POTASSIUM, SODIUM,

CALCIUM & MAGNESIUM NATURALLY INCREASING THE

ALKALINITY OF THE WATER

ACTIVATED OXYGEN INJECTION

O3 STERILIZES THE HOLDING TANK AFTER 8 HOURS OF NONUSE

Our systems are tested and certified to the highest industry standards for safety and performance. The 4i is certified by IAPMO in accordance with ANSI/NSF 372 for lead free products and certified by IAPMO R&T in accordance with UL 399 and CSA 22.2 for electrical safety.

TO ORDER CALL 718-313-0113

4IK TOUCHLESS SENSOR-ACTIVATED WATER PURIFICATION SYSTEM

6





√∭(•

(%)

Touchless

Sensor Activation

Hygienic, touchfree operation.

Anti-Microbial

Anti-microbial

additive maintains cleanliness of unit

High-Capacity

Drip Tray

Optional drain

11.7"W x 19.5"D x 17.8"H

connection prevents need for emptying.

Surface

exterior.

SPECIFICATIONS



